

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M12X90

Article number	01000.120.090
Brand	-
UBB	950351008178
UNSPSC	31161620
EAN	8715492008039
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	36
b (min.): $L > 200$ mm	49
b (min.): $L \leq 125$ mm	30
d-D	M12
k	7.5
L (mm)	90
P	1.75
s	19

Technical Drawing

