

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M12X110

Article number	01000.120.110
Brand	-
UBB	950351008335
UNSPSC	31161620
EAN	8715492008060
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ISO	4014
NEN	1555
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	36
b (min.): $L > 200$ mm	49
b (min.): $L \leq 125$ mm	30
d-D	M12
k	7.5
L (mm)	110
P	1.75
s	19

Technical Drawing

