

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M12X140

Article number	01000.120.140
Brand	-
UBB	950351008665
UNSPSC	31161620
EAN	8715492008091
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	140
P	1.75
s	19

Technical Drawing

