

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M14X50

Article number	01000.140.050
Brand	-
UBB	950351009655
UNSPSC	31161620
EAN	8715492008244
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	40
b (min.): $L > 200$ mm	53
b (min.): $L \leq 125$ mm	34
d-D	M14
k	8.8
L (mm)	50
P	2
s	22

Technical Drawing

