

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M14X60

Article number	01000.140.060
Brand	-
UBB	950351009812
UNSPSC	31161620
EAN	8715492008268
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	40
b (min.): $L \geq 200$ mm	53
b (min.): $L \leq 125$ mm	34
d-D	M14
k	8.8
L (mm)	60
P	2
s	22

Technical Drawing

