

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M14X75

Article number	01000.140.075
Brand	-
UBB	950351010133
UNSPSC	31161620
EAN	8715492008299
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200$ mm	40
b (min.): $L \geq 200$ mm	53
b (min.): $L \leq 125$ mm	34
d-D	M14
k	8.8
L (mm)	75
P	2
s	22

Technical Drawing

