

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M16X65

|                |               |
|----------------|---------------|
| Article number | 01000.160.065 |
| Brand          | -             |
| UBB            | 950351011537  |
| UNSPSC         | 31161620      |
| EAN            | 8715492008527 |
| PKG. of 25     | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M16           |
| Length            | 65 mm         |
| Class             | 8.8           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

### Standards

|      |            |
|------|------------|
| NEN  | 1555       |
| NF   | E25-112    |
| ISO  | 4014       |
| ASME | B18.2.3.1M |
| DIN  | 931        |

### Technical Specification

|                                    |     |
|------------------------------------|-----|
| b (min.):<br>125mm $L \leq 200$ mm | 44  |
| b (min.): $L > 200$ mm             | 57  |
| b (min.): $L \leq 125$ mm          | 38  |
| d-D                                | M16 |
| k                                  | 10  |
| L (mm)                             | 65  |
| P                                  | 2   |
| s                                  | 24  |

### Technical Drawing

