

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M18X75

Article number	01000.180.075
Brand	-
UBB	950351013772
UNSPSC	31161620
EAN	8715492008886
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	48
b (min.): $L > 200$ mm	61
b (min.): $L \leq 125$ mm	42
d-D	M18
k	11.5
L (mm)	75
P	2.5
s	27

Technical Drawing

