

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M18X80

Article number	01000.180.080
Brand	-
UBB	950351013855
UNSPSC	31161620
EAN	8715492008893
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	48
b (min.): $L > 200$ mm	61
b (min.): $L \leq 125$ mm	42
d-D	M18
k	11.5
L (mm)	80
P	2.5
s	27

Technical Drawing

