

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M20X90

Article number	01000.200.090
Brand	-
UBB	950351015835
UNSPSC	31161620
EAN	8715492009203
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
NEN	1555
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	52
b (min.): $L > 200$ mm	65
b (min.): $L \leq 125$ mm	46
d-D	M20
k	12.5
L (mm)	90
P	2.5
s	30

Technical Drawing

