

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X200



Article No.	01000.200.200
Brand	-
UBB	950351016742
UNSPSC	31161620
EAN	8715492009340
PKG. of 10	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M20
Length (L) (mm)	200

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	52
b (min.): $L > 200\text{mm}$	65
b (min.): $L \leq 125\text{mm}$	46
k	12.5
P	2.50
s	30

Technical Drawing

