

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X250



Article No.	01000.200.250
Brand	-
UBB	950351914771
UNSPSC	31161620
EAN	8715492009395
PKG. of 10	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M20
Length (L) (mm)	250

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	52
b (min.): $L > 200\text{mm}$	65
b (min.): $L \leq 125\text{mm}$	46
k	12.5
P	2.50
s	30

Technical Drawing

