

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M20X280

Article number	01000.200.280
Brand	-
UBB	950351017161
UNSPSC	31161620
EAN	8715492009418
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	280 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	280
P	2.5
s	30

Technical Drawing

