

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M20X300

|                |               |
|----------------|---------------|
| Article number | 01000.200.300 |
| Brand          | -             |
| UBB            | 950351017245  |
| UNSPSC         | 31161620      |
| EAN            | 8715492009425 |
| PKG. of 10     | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M20           |
| Length            | 300 mm        |
| Class             | 8.8           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

### Standards

|      |            |
|------|------------|
| ASME | B18.2.3.1M |
| DIN  | 931        |
| ISO  | 4014       |
| NF   | E25-112    |
| NEN  | 1555       |

### Technical Specification

|                                    |      |
|------------------------------------|------|
| b (min.):<br>125mm $L \leq 200$ mm | 52   |
| b (min.): $L \geq 200$ mm          | 65   |
| b (min.): $L \leq 125$ mm          | 46   |
| d-D                                | M20  |
| k                                  | 12.5 |
| L (mm)                             | 300  |
| P                                  | 2.5  |
| s                                  | 30   |

### Technical Drawing

