

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M22X180

Article number	01000.220.180
Brand	-
UBB	950351018987
UNSPSC	31161620
EAN	8715492009630
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M22
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	56
b (min.): $L > 200$ mm	69
b (min.): $L \leq 125$ mm	50
d-D	M22
k	14
L (mm)	180
P	2.5
s	32

Technical Drawing

