

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M24X130

Article number	01000.240.130
Brand	-
UBB	950351020298
UNSPSC	31161620
EAN	8715492009869
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	60
b (min.): $L > 200$ mm	73
b (min.): $L \leq 125$ mm	54
d-D	M24
k	15
L (mm)	130
P	3
s	36

Technical Drawing

