

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M24X210

Article number	01000.240.210
Brand	-
UBB	950351915018
UNSPSC	31161620
EAN	8715492009944
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	210 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	60
b (min.): $L > 200$ mm	73
b (min.): $L \leq 125$ mm	54
d-D	M24
k	15
L (mm)	210
P	3
s	36

Technical Drawing

