

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M24X400

Article number	01000.240.400
Brand	-
UBB	950351021775
UNSPSC	31161620
EAN	8715492010100
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	400 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	60
b (min.): $L \geq 200$ mm	73
b (min.): $L \leq 125$ mm	54
d-D	M24
k	15
L (mm)	400
P	3
s	36

Technical Drawing

