

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M24X420

Article number	01000.240.420
Brand	-
UBB	950351021858
UNSPSC	31161620
EAN	8715492010117
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	420 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	60
b (min.): $L > 200$ mm	73
b (min.): $L \leq 125$ mm	54
d-D	M24
k	15
L (mm)	420
P	3
s	36

Technical Drawing

