

Hexagon head bolt DIN 931 Steel Plain 8.8 M27X90



Article No.	01000.270.090
Brand	-
UBB	950351022195
UNSPSC	31161620
EAN	8715492010179
PKG. of 10	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M27
Length (L) (mm)	90

Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	66
b (min.): $L > 200\text{mm}$	79
b (min.): $L \leq 125\text{mm}$	60
k	17
P	3
s	41

Technical Drawing

