

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M27X100

Article number	01000.270.100
Brand	-
UBB	950351022278
UNSPSC	31161620
EAN	8715492010186
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	100
P	3
s	41

Technical Drawing

