

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M27X150

Article number	01000.270.150
Brand	-
UBB	950351022765
UNSPSC	31161620
EAN	8715492010230
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	150
P	3
s	41

Technical Drawing

