

Hexagon head bolt DIN 931 Steel Plain 8.8 M27X320



Article No.	01000.270.320
Brand	-
UBB	950351023839
UNSPSC	31161620
EAN	8715492010377
PKG. of 5	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M27
Length (L) (mm)	320

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	66
b (min.): $L > 200\text{mm}$	79
b (min.): $L \leq 125\text{mm}$	60
k	17
P	3
s	41

Technical Drawing

