

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X140



Article No.	01000.300.140
Brand	-
UBB	950351024829
UNSPSC	31161620
EAN	8715492010506
PKG. of 10	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M30
Length (L) (mm)	140

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	72
b (min.): $L > 200\text{mm}$	85
b (min.): $L \leq 125\text{mm}$	66
k	18.7
P	3.50
s	46

Technical Drawing

