

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M30X190

Article number	01000.300.190
Brand	-
UBB	950351025321
UNSPSC	31161620
EAN	8715492010551
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M30
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	72
b (min.): $L > 200$ mm	85
b (min.): $L \leq 125$ mm	66
d-D	M30
k	18.7
L (mm)	190
P	3.5
s	46

Technical Drawing

