

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X300



Article No.	01000.300.300
Brand	-
UBB	950351025990
UNSPSC	31161620
EAN	8715492010643
PKG. of 5	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M30
Length (L) (mm)	300

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	72
b (min.): $L > 200\text{mm}$	85
b (min.): $L \leq 125\text{mm}$	66
k	18.7
P	3.50
s	46

Technical Drawing

