

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M33X140

Article number	01000.330.140
Brand	-
UBB	950351027145
UNSPSC	31161620
EAN	8715492010810
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
NEN	1555
ISO	4014
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	78
b (min.): $L > 200$ mm	91
b (min.): $L \leq 125$ mm	72
d-D	M33
k	21
L (mm)	140
P	3.5
s	50

Technical Drawing

