

Hexagon head bolt DIN 931 Steel Plain 8.8 M36X100



Article No.	01000.360.100
Brand	-
UBB	500621727675
UNSPSC	31161620
EAN	8715494501699
PKG. of 5	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M36
Length (L) (mm)	100

Standards

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	84
b (min.): $L > 200\text{mm}$	97
b (min.): $L \leq 125\text{mm}$	78
k	22.5
P	4
s	55

Technical Drawing

