

## Hexagon head bolt DIN 931 Steel Plain 8.8 M39X160



Article No.	01000.390.160
Brand	-
UBB	950351031188
UNSPSC	31161620
EAN	8715492011435
PKG. of 1	Full Box Only

### Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M39
Length (L) (mm)	160

### Standards

DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	90
b (min.): $L > 200\text{mm}$	103
b (min.): $L \leq 125\text{mm}$	84
k	25
P	4
s	60

### Technical Drawing

