

Hexagon head bolt DIN 931 Steel Plain 8.8 M45X200



Article No.	01000.450.200
Brand	-
UBB	950351034315
UNSPSC	31161620
EAN	8715492011909
PKG. of 1	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M45
Length (L) (mm)	200

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	102
b (min.): $L > 200\text{mm}$	115
b (min.): $L \leq 125\text{mm}$	96
k	28
P	4.50
s	70

Technical Drawing

