

## Hexagon head bolt DIN 931 Steel Plain 8.8 M56X180



Article No.	01000.560.180
Brand	-
UBB	950351036880
UNSPSC	31161620
EAN	8715492012456
PKG. of 1	Full Box Only

### Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M56
Length (L) (mm)	180

### Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	124
b (min.): $L > 200\text{mm}$	137
k	35
P	5.50
s	85

### Technical Drawing

