



DIN 609 Hexagon Fit Bolt with Long Thread, Plain, 8.8 M14X70X47

Article number	01040.140.070
Brand	-
UBB	500644609215
UNSPSC	31161620
EAN	8717077009479
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M14
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	609
-----	-----

Technical Specification

b:50mmL≤150mm	24
b (min.): L150mm	29
b:L≤50mm	22
d-D	M14
ds (k6)	15
k	8.8
L (mm)	70
Lg (max.)	47
P	2
s	21
Tolerance drill ø	H7

Technical Drawing

