



DIN 960 Partially Threaded Metric Extra Fine Hexagon Head Bolt, Plain, Class 8.8 M18X1,50X100

Article number	01061.180.100
Brand	-
UBB	950351133075
UNSPSC	31161620
EAN	8715492020871
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Standards

DIN	960
NEN	1555
NF	E25-152
ISO	8765

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	100
P	1.5
s	27

Technical Drawing

