



DIN 561 Hexagon Head Bolt with Full Dog Point, Plain, Class 22H M6X12

Číslo položky 01098.060.012

Značka -

UBB 952351212412

UNSPSC 31161620

EAN 8715492022554

PKG. of 200 Len kompletne balenie

Technické parametre

Diameter	M6
Length	12 mm
Threaded pitch (P)	1
Class	22H
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Point	Dog
Surface treatment	Plain
Thread	Metric thread

Normy

NF	E25-133
DIN	561

Technické špecifikácie

d-D	M6
dp (max.)	4
k	5
L (mm)	12
P	1
s	8
z2 (min.)	3

Technický náčrt

