



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M5X70

Article number	01200.050.070
Brand	-
UBB	950351141318
UNSPSC	31161620
EAN	8715492024831
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	70
P	0.8
s	8

Technical Drawing

