



## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M6X70

|                |               |
|----------------|---------------|
| Article number | 01200.060.070 |
| Brand          | -             |
| UBB            | 950351142308  |
| UNSPSC         | 31161620      |
| EAN            | 8715492024961 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M6            |
| Length            | 70 mm         |
| Class             | 8.8           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Zinc plated   |
| Thread            | Metric thread |

### Standards

|      |            |
|------|------------|
| NEN  | 1555       |
| ASME | B18.2.3.1M |
| NF   | E25-112    |
| DIN  | 931        |
| ISO  | 4014       |

### Technical Specification

|                           |    |
|---------------------------|----|
| b (min.):<br>125mmL≤200mm | 24 |
| b (min.): L≤125mm         | 18 |
| d-D                       | M6 |
| k                         | 4  |
| L (mm)                    | 70 |
| P                         | 1  |
| s                         | 10 |

### Technical Drawing

