

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M6X120



Article number	01200.060.120
Brand	-
UBB	950351142977
UNSPSC	31161620
EAN	8715492025043
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	120
P	1
s	10

Technical Drawing

