

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M6X130



Article number	01200.060.130
Brand	-
UBB	951351959725
UNSPSC	31161620
EAN	8715492025067
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	24
b (min.): $L \leq 125$ mm	18
d-D	M6
k	4
L (mm)	130
P	1
s	10

Technical Drawing

