

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M6X140



Article number	01200.060.140
Brand	-
UBB	952351072816
UNSPSC	31161620
EAN	8715492025081
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	24
b (min.): $L \leq 125$ mm	18
d-D	M6
k	4
L (mm)	140
P	1
s	10

Technical Drawing

