



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M7X50

Article number	01200.070.050
Brand	-
UBB	950351143470
UNSPSC	31161620
EAN	8715492025159
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M7
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	26
b (min.): L≤125mm	20
d-D	M7
k	4.8
L (mm)	50
P	1
s	11

Technical Drawing

