

Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M8X120



Article number	01200.080.120
Brand	-
UBB	950351145111
UNSPSC	31161620
EAN	8715492025357
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	120
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	28
b (min.): $L \leq 125\text{mm}$	22
k	5.3
P	1.25
s	13

Technical Drawing

