



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M10X45/S=17

Article number	01200.100.045
Brand	-
UBB	950351145947
UNSPSC	31161620
EAN	8715492025456
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
NEN	1555
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	45
P	1.5
s	17

Technical Drawing

