



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M10X60/S=17

Article number	01200.100.060
Brand	-
UBB	950351146283
UNSPSC	31161620
EAN	8715492025517
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L > 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	60
P	1.5
s	17

Technical Drawing

