



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M10X120/S=17

Article number	01200.100.120
Brand	-
UBB	950351147190
UNSPSC	31161620
EAN	8715492025708
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L \geq 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	120
P	1.5
s	17

Technical Drawing

