

Hexagon head bolt DIN 931 Steel Zinc plated 8.8 M10X140/S=17



Article number	01200.100.140
Brand	-
UBB	950351147356
UNSPSC	31161620
EAN	8715492025739
PKG. of 50	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	140
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Wrench width (s) (mm)	17

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	32
b (min.): L>200mm	45
b (min.): L≤125mm	26
k	6.4
P	1.50
s	17

Technical Drawing

