



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M10X150/S=17

Article number	01200.100.150
Brand	-
UBB	950351147430
UNSPSC	31161620
EAN	8715492025746
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	931
NF	E25-112
NEN	1555
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L \geq 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	150
P	1.5
s	17

Technical Drawing

