



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M10X210/S=17

Article number	01200.100.210
Brand	-
UBB	955351314609
UNSPSC	31161620
EAN	8715493753549
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	210 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	210
P	1.5
s	17

Technical Drawing

