



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M12X40/S=19

Article number	01200.120.040
Brand	-
UBB	500621729655
UNSPSC	31161620
EAN	8715494503556
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	36
b (min.): $L > 200$ mm	49
b (min.): $L \leq 125$ mm	30
d-D	M12
k	7.5
L (mm)	40
P	1.75
s	19

Technical Drawing

