



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M12X50

Article number	01200.120.051
Brand	-
UBB	952351614294
UNSPSC	31161620
EAN	8715492025869
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	50
P	1.75
s	18

Technical Drawing

