



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M16X140

Article number	01200.160.140
Brand	-
UBB	950351153362
UNSPSC	31161620
EAN	8715492026682
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L \geq 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	140
P	2
s	24

Technical Drawing

